



DIMENSIONS

TERMINATION



CONTACT ARRANGEMENT

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
a	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×
b	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×
c	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×	×

☒ STANDARD CONTACT
 ☐ EMPTY CAVITY
 ☒ FMLB GROUNDING CONTACT

PART NUMBER


86093967896755GDLF

GENERAL CHARACTERISTICS & RoHS INFO

REFER DRAWING C-8609-0000C

mat'l. code SEE DWG C-8609-0000C				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family 8609			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title DIN REVERSE HEADER DIN 41612 STYLE R PRESSFIT REAR PLUG-UP			
A	I10-0043	KR	2010-02-08	angles	linear	0.X ± 0.1	scale 3:2			
						0.XX ± 0.1				
				0° ± 2°		0.XXX ± 0.1				
				dr	KESAVAN R	2010-02-08	FCI			
				engr	KESAVAN R	2010-02-08				
				chr	KESAVAN R	2010-02-08				
				appd	BIJU K PAUL	2010-02-08				
sheet index	revision sheet	A	1				dwg no C-8609-2238			
							sheet 1 of 1 size A3			
							type 3 Drawing			

PCB LAYOUT



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)
[86093967896755GDLF](#)