

1

2


3

4


|                   |                |                |                |                |
|-------------------|----------------|----------------|----------------|----------------|
| Cable Kits P/N    | 10089331-101LF | 10089331-102LF | 10089331-103LF | 10089331-104LF |
| Lock Screw Length | 12.50          | 12.50          | 15.00          | 15.00          |
| AWG               | 24&26          | 28&30          | 24&26          | 28&30          |

A



B



C



D



|               |                                       |         |       |       |             |            |                                   |                           |                |                     |          |           |          |   |
|---------------|---------------------------------------|---------|-------|-------|-------------|------------|-----------------------------------|---------------------------|----------------|---------------------|----------|-----------|----------|---|
| spec ref      |                                       | *       |       | dr    | Junor Huang | 2008-06-03 | <div>projection</div> <div></div> | <div>MM</div> <div></div> | size           | A4                  | scale    | 1.500     |          |   |
| tolerance std | TOLERANCES UNLESS OTHERWISE SPECIFIED |         |       | eng   | De-Feng Qin | 2011-07-19 |                                   |                           | ecn no         | ECR-ELX-DG-005201-2 |          |           |          |   |
|               |                                       |         |       | chr   | -           | -          |                                   |                           |                |                     |          |           |          |   |
|               |                                       |         |       | appr  | PM ZHENG    | 2011-07-19 |                                   |                           | product family |                     |          | rel level | Released |   |
| surface       | <div>✓</div>                          | linear  | 0.X   | ±0.3  |             | title      | 64 pos VDSL                       |                           |                | dwg no              | 10089331 |           | rev      | F |
|               |                                       |         | 0.XX  | ±0.15 |             |            |                                   |                           |                |                     |          |           |          |   |
|               |                                       |         | 0.XXX | ±0.05 |             |            |                                   |                           |                |                     |          |           |          |   |
|               |                                       | angular | 0°    | ± 2 ° |             |            |                                   |                           |                |                     |          |           |          |   |

ProE File - REV C - 2009-08-09

1

2

3


4

# BOM of cable kits 10089331

| Component Name | Cable Clamp | Cover TOP | Cover Bottom | Screw lock with cover | Screw Lock with board conn. | Assembled Terminal Block | Shroud |
|----------------|-------------|-----------|--------------|-----------------------|-----------------------------|--------------------------|--------|
| Qt'y/Kit       | 1           | 1         | 1            | 4                     | 2                           | 2                        | 1      |

## NOTE:

1. This product is not intended to be exposed to a manufacturing solder process.
2. Material:  
Diacasting : Zn alloy with cu ,nickel & pure tin plating  
Shroud: PBT  
Terminal; Copper alloy  
Screw: stainless steel
3. Cable O.D:9.7mm-11mm.



|               |                                       |         |       |       |             |            |                                                             |                        |          |          |       |
|---------------|---------------------------------------|---------|-------|-------|-------------|------------|-------------------------------------------------------------|------------------------|----------|----------|-------|
| spec ref      |                                       | *       |       | dr    | De-Feng Qin | 2011-07-19 | <div>projection</div> <div></div> <div>MM</div> <div></div> | size                   | A4       | scale    | 2.000 |
| tolerance std | TOLERANCES UNLESS OTHERWISE SPECIFIED |         |       | eng   | De-Feng Qin | 2011-07-19 |                                                             | ecn no                 |          |          |       |
|               |                                       |         |       | chr   | PM ZHENG    | 2011-07-19 |                                                             | rel level              |          |          |       |
|               |                                       |         |       | appr  | Joseph Hsia | 2011-07-19 |                                                             | product family         |          | Released |       |
| surface       | ✓                                     | linear  | 0.X   | ±0.3  |             | title      | 64 pos VDSL                                                 | dwg no                 | 10089331 | rev      | F     |
|               |                                       |         | 0.XX  | ±0.15 |             |            |                                                             |                        |          |          |       |
|               |                                       |         | 0.XXX | ±0.05 |             |            |                                                             |                        |          |          |       |
|               |                                       | angular | 0°    | ± 2 ° | www.fci.com | cat. no.   | *                                                           | Product - Customer Drw |          | sheet 2  | of 2  |

Proj File - REV C - 2009-08-09

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10089331-103LF](#) [10089331-104LF](#)