

1


2

3

4


A

A





B

B




C

C



DETAIL OF LOCATING PEGS (2x) SCALE 8/1



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE PRODUCT SPECIFICATION GS-12-446


OTHERS INFORMATIONS, SEE DRW C-8626-11210-2

European Views

Copyright FCI.




D

D



REV F - 2006-04-17

rev	ecn no	dr	date
C	-	CHA	2003/03/18
D	LS06-0089	LGO	2006/06/06
E	LS07-0184	MLE	2007/07/27
F	DG-13365	QinDF	2012/10/07
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	CHAMPION	18/03/03	ANGULAR	LINEAR	0.X	± 0.1	size A3	Scale 4: 1			
Eng	LENOIR	18/03/03			0.XX	± 0.1					
Chr	LEGARE	18/03/03			0.XXX	± 0.1					
Appr	LEGARE	18/03/03	Product family				METRAL	ECN LS07-0184 Spec ref -			
			title METRAL RA HEADER WB CONV 4x6 CTS -STB- PUSH PEG				dwg no C-8626-11210-1			Rev F	
			catalog no -				CUSTOMER			sheet 1 of 2	

PDS: Rev: F

STATUS: Released

Printed: Nov 06, 2012

4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM1L41AAP426H6PLF](#) [HM1L41ZAP435H6PLF](#)