










FCI CONFIDENTIAL




PART NUMBER
10119834-001LF




- NOTES:
1. MATERIAL: LCP, UL94 V-0, COLOR: NATURAL.
HOUSING: 11-CU.
CAP: STAINLESS STEEL.
TERMINAL: 11-CU.
BOARDLOCK: STAINLESS STEEL.
 2. FINISH: CONTACT AREA: GOLD PL.30u" THK.MIN.
ALL AREA: GOLD PL.1u" THK.MIN.
UNDER PLUNCKEL PL.50u" THK.MIN.
BOARDLOCK: ALL AREA: GOLD PL.1u" THK.MIN.
UNDER PLUNCKEL PL.50u" THK.MIN.
 3. NORMAL FORCE :0.85N Min. FOR 0.90mm COMPRESSION .
 4. CP RETENTION FORCE : 9.8N Min.
 5. THE PRODUCT SEPC. PLS. REFER TO GS-12-674
 6. THE PACKAGING SPEC. PLS. REFER TO GS-14-1545
 7. THIS CONNECTOR CAN WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN IR REFLOW OVEN.
 8. THE SUFFIX "LF" MEANS FOR LEAD FREE PROCESS.



RECOMMENDED PCB LAYOUT
TOLERANCE+/-0.05





rev	ecn no	dr	date
A	NEW	HT	2012-05-10
B	ELX-DG-012625	VL	2012-08-15
C	ELX-DG-012610	VL	2012-08-24
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-



TOLERANCES UNLESS
OTHERWISE SPECIFIED

dr	HT ZHANG	2012-05-10
eng	HT ZHANG	2012-05-10
chr	HT ZHANG	2012-05-10
appr	PM ZHENG	2012-05-10



size	scale
A4	1 : 1

NO.	DESCRIPTION	QTY
4	CAP	1PCS
3	BOARD LOCK	1PCS
2	HOUSING	1PCS
1	TERMINAL	4PCS

0.X	± 0.25
0.XX	± 0.15
0.XXX	± 0.10
angular	± 1°



4PIN 3.60mm PITCH BATTERY
MOBILE BATTERY CONNECTOR

10119834

rev C

PROT FILE -- REV C -- 2012-05-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10119834-001LF](#)