

FRONT ACCESSORY	Blank without	LOinsert M3 insert UNC 4.40
PCB ACCESSORIES	AA without	AA without

PART NUMBER	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxSA00LF	200	without	without
D*LxWxSA00LF	200	insert M3	without
D*OxWxSA00LF	200	insert UNC 4.40	without
D*xWxS043A00LF	500	without	without
D*LxWxS043A00LF	500	insert M3	without
D*OxWxS043A00LF	500	insert UNC 4.40	without

shell size	LAYOUTS
*	xWx
E	5W1
A	11W1
A	7W2
B	21W1
B	17W2
B	13W3
B	9W4
C	25W3
C	21WA4
C	27W2
D	47W1
D	24W7
D	36W4

FCI
Copyright FCI.




www.fciconnect.com			surface - <input checked="" type="checkbox"/>		tolerance std		projection		mm		
			ISO 1302		ISO 406 ISO 1101						
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X		±0.3		size A2	Scale 2:1	
Eng	P LEGARE	2005-10-11			0.XX		±0.1				
Chr					0.XXX		±0.05				
Appr			0° ±2°		ECN		LS07-0273				
Product family					- Spec ref						
		title SUB FEMALE DW				dwg no C01-8639-2303			Rev. D		
		mixed power+solder bucket				CUSTOMER			sheet 2 of 7		
		catalog no				-					

SCALE: 4








5W1

11W1

7W2







SIDE VIEW FOR
LAYOUTS: E A B C



Floating signal contacts



Copyright FCI.

www.fciconnect.com			surface - 		tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 2:1		
Eng	P LEGARE	2005-10-11			0.XX	±0.1		ECN LS07-0273		
Chr					0° ±2°	±0.05				
Appr			Product family			-	Spec ref			
			title SUB FEMALE DW				dwg no C01-8639-2303		Rev D	
			mixed power+solder bucket							
			catalog no -				CUSTOMER		sheet 3 of 7	

REV E - 2006-03-28

PDS: Rev :D

PDM: Rev :D







STATUS: Released

Printed: Jun 19, 2015





13W3


9 W 4

17W2



Floating signal contacts



www.fciconnect.com			surface 		tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 2:1		
Eng	P LEGARE	2005-10-11			0.XX	±0.1				
Chr					0.XXX	±0.05				
Appr			Product family			- Spec ref				
		title SUB FEMALE DW mixed power+solder bucket	dwg no C01-8639-2303				Rev. D			
catalog no		-	CUSTOMER		sheet 4 of 7					







Copyright FCi.






24W7



www.fciconnect.com			surface <input checked="" type="checkbox"/>		tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	2005-10-11	ANGULAR LINEAR		0.X	±0.3	size	Scale		
Eng	P LEGARE	2005-10-11			0.XX	±0.1	A2		2:1	
Chr					0.XXX	±0.05	ECN		LS07-0273	
Appr			Product family				-	Spec ref		
			title SUB FEMALE DW mixed power+solder bucket				dwg no C01-8639-2303		Rev D	
			catalog no				-	CUSTOMER		sheet 6 of 7



www.fciconnect.com			surface <input checked="" type="checkbox"/> ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale		
Eng	P LEGARE	2005-10-11			0.XX	±0.1		2:1		
Chr					0.XXX	±0.05		ECN LS07-0273		
Appr			Product family				-	Spec ref		
			title SUB FEMALE DW				dwg no C01-8639-2303		Rev. D	
			mixed power+solder bucket							
			catalog no				-	CUSTOMER	sheet 7 of 7	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DA11W1S043A00LF](#) [DAL7W2SA00LF](#) [DAO11W1SA00LF](#) [DBO17W2SA00LF](#) [DD47W1SA00LF](#)
[DB17W2S043A00LF](#) [DBO17W2S043A00LF](#) [DCO21WA4SA00LF](#) [DBO9W4SA00LF](#) [DBL9W4S043A00LF](#)