




ROHS PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	Gold Flash	0.76µ Gold	1.25µ Gold
09	30.81	24.99	16.96	16.79	10.96	D09P90C4GL00LF	D09P90C6GL00LF	D09P90C8GL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P90C4GL00LF	D15P90C6GL00LF	D15P90C8GL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P90C4GL00LF	D25P90C6GL00LF	D25P90C8GL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P90C4GL00LF	D37P90C6GL00LF	D37P90C8GL00LF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001



PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406 ISO 1101		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
H	ELX-I-12654	AB	2015-10-26	angles	linear	mm	MALE DELTA-D LOW PROFILE		
J	ELX-I-24020	AAB	2016-06-06	0°±2°	linear	scale 2:1	STRAIGHT PRESS-FIT		
				dr	PESSON	1995-10-03	dwg no	sheet 1 of 1	size
				enrg	MITHUN PAUL	2016-06-06	C01-8646-0369		
				chr	ATHUL A.B	2016-06-06	A3		
				appd	BIJU K PAUL	2016-06-06	type Product Customer Drawing		
sheet index	revision	J							
	sheet	1							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[D37P90C6GL00LF](#)