





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1550159~162	2015/05/25	Vicky	Update Logo



GBD-08BFFM-TL7AXX
XX: 01~99Meter
01: 01Meter
02: 02Meters
...
99: 99Meters
Cable Length(L): 01~99Meters



Conn.
Pin Assignments
Front View

1	Black (24AWG)	黑
2	Brown (24AWG)	棕
3	Red (24AWG)	紅
4	Orange (24AWG)	橘
5	Yellow (24AWG)	黃
6	Purple (24AWG)	紫
7	Green (20AWG)	綠
8	Blue (20AWG)	藍
Conn.	Wire Color	

- Note:
- * $\varnothing$ Important Dimension To Check
 - * Waterproof Rate: IP67
 - * Connector: PBT+PC, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 (20#*2C+24#*6C)+D+A, Black, PVC Jacket, UV Resistant, OD=6.0mm
 - * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm				TITLE 三點卡合 G Size Cable Lock 8P F Conn F Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY		DATE					
TOLERANCE ±0.5 mm		SCALE 1:1						SIZE A4		SHEET 1 OF 1		DWG NO GBD-08BFFM-TL7AXX		CHECKED BY Rita		DATE 2015-05-25	
		REV. B						WC-REV. A.1		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Lion		DATE 2015-05-25	
1		2		3		4		5		6		7		8 FMM10702-01-02A1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[GBD-08BFFM-TL7A10](#) [GBD-08BFFM-TL7A05](#) [GBD-08BFFM-TL7A01](#) [GBD-08BFFM-TL7A02](#)