



CONTACT SIZE	SHELL SIZE	X	Y ±.040
16 SHORT	10SL, 14S, 16S	.087±.039	.079
16 LONG	14, 16, THRU 40	.260 ⁺ .052 .041	.102
12	14, 16, THRU 40	.118 ⁺ .039 .056	.102
4,8,0	14, 16, THRU 40	.091±.039	.102

REVISIONS			
ZONE	LTR	DESCRIPTION	DATE
	A	INITIAL RELEASE NUM: 10090-312	
	B	(CL II) SEE ECN 27939	7-21-93 Rotochuk
	C	(CL II) REMOVED ITEM #2, NOTE 9, & 9-1936 FROM NOTE #5 ECN: A0677	10/19/06 BROOKER



SEE SHEET 2
NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.


COMPANY ID: 2
CODED/MS/CUST: Y
INTERNAL: N
LOTNO: N
DATE CODE: 9-3895
SEE PRINT: N

N/A
N/A
NEXT ASSEMBLY

UNLESS OTHERWISE SPECIFIED
LINEAR DIMENSIONS ARE IN INCHES.
TOLERANCES: .XXX±.010,
.XX ±.03, .X ±.1, ANGLES ±2°
OTHER STANDARDS PER 9-3800
AND DOD-D-1000. NOTE REF= (XX)

5	SEE NOTE 10	CONTACT	3
4	I	10-748XX-XXX	INSERT
3	I	10-564867-XX3	ADAPTER
2		REMOVED	9
1	I	SEE COLUMN	SHELL

FIND NO.	QTY REQD.	FSCM NO.	PART NUMBER	DESCRIPTION	NOTE REF.
PARTS LIST					
SPECIFICATIONS		SIGNATURES	DATES	AMPHENOL CORPORATION BENDIX CONNECTOR OPERATIONS SIDNEY, N.Y.	
MATERIAL SPEC.		PREPARED MCELLIGOTT	08/29/90	CONNECTOR, ELECTRICAL RECEPTACLE, FRONT PANEL MOUNT, REVERSE BAYONET COUPLING, TYPE GTC00A()-(). SOLDERLESS	
N/A		CHECKED [Signature]	11/1/90		
PROCESS SPEC.		APPROVED [Signature]	11/1/90		
SEE NOTE 5		1ST PART NO. 71-580124-22S	9-9-90		
SCALE: NONE		SIZE: D	FSCM NO: 77820	REF: 71-580470/489	REV. C
		WT:		SHEET 1 OF 2	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[GTC00A24-10S\(RDS\)\(023\)](#) [GTC00A24-10S\(RDS\)\(025\)](#) [GTC00A20-19S\(RDS\)](#) [GTC00A24-10S\(RDS\)](#) [GTC00A28-6S\(RDS\)](#) [GTC00A32-15S\(RDS\)](#) [GTC00A2022S](#) [GTC00A4010PW](#) [GTC00A4010P](#) [GTC00A20-22SW](#) [GTC00A2222PLC](#) [GTC00A2866P](#) [GTC00A2222PXLC](#) [GTC00A-20-15SLC](#) [GTC00A2222PX](#) [GTC00A14S5S](#) [GTC00A28AYP](#) [GTC00A202P](#) [GTC00A203PW](#) [GTC00A203P](#) [GTC00A-24-10S](#) [GTC00A14S-6S-B30](#) [GTC00A22-22SX-RDS](#) [GTC00A18-1PZ](#) [GTC00A18-1PX](#) [GTC00A28-6SW-RDS](#) [GTC00A22-22S-RDS](#) [GTC00A18-1PY](#) [GTC00A18-1PW](#) [GTC00A32-79P](#) [GTC00A20-19P](#) [GTC00A20-33P-LC](#) [GTC00A24-10P](#) [GTC00A24-22P](#) [GTC00A20-15P](#) [GTC00A20-29S](#) [GTC00A18-22S](#) [GTC00A18-1P](#) [GTC00A20-58S](#) [GTC00A20-29P](#) [GTC00A20-3S-F0](#) [GTC00A36-77SW-RDS](#) [GTC00A36-77SX-RDS](#) [GTC00A36-77S-RDS](#) [GTC00A-20-4P](#) [GTC00A36-10S](#) [GTC00A36-10PX](#) [GTC00A-32-20S](#) [GTC00A286S](#) [GTC00A2022P](#) [GTC00A286P](#) [GTC00A3215S](#) [GTC00A22-14P-LC](#) [GTC00A10SL-3P](#) [GTC00A10SL-3S](#) [GTC00A10SL-4P](#) [GTC00A18-10S](#) [GTC00A18-10P](#) [GTC00A22-14P](#) [GTC00A22-22S](#) [GTC00A22-20P](#) [GTC00A22-14S](#) [GTC00A20-29P-LC](#) [GTC00A20-22S-RDS](#) [GTC00A20-2S](#) [GTC00A18-11S](#) [GTC00A18-11P](#) [GTC00A22-23P](#) [GTC00A22-9S](#) [GTC00A32-17S](#) [GTC00A28-21P](#) [GTC00A28-22S](#) [GTC00A32-7S](#) [GTC00A32-6S](#) [GTC00A28-10S](#) [GTC00A32-5S](#) [GTC00A36-4P](#) [GTC00A22-23S](#) [GTC00A36-77S](#) [GTC00A36-5S](#) [GTC00A36-4S](#) [GTC00A22-7S-RDS](#) [GTC00A28-21PX](#) [GTC00A22-2SW-RDS](#) [GTC00A22-2S-RDS](#) [GTC00A40-80P](#) [GTC00A28-21PW](#) [GTC00A22-22SX](#) [GTC00A22-21S-RDS](#) [GTC00A28-6S-LC](#) [GTC00A28-AYS](#) [GTC00A36-3P](#) [GTC00A24-28P-LC](#) [GTC00A24-22S](#) [GTC00A24-28P](#) [GTC00A28-10P](#) [GTC00A28-15S](#) [GTC00A20-3S](#) [GTC00A36-7S](#) [GTC00A36-14P](#)