



CONTACT SIZE	SHELL SIZE	X	Y ±.040
16 SHORT	10SL, 14S, 16S	.087±.039	.079
16 LONG	14, 16, THRU 40	.260 ^{±.052} _{±.041}	.102
12	14, 16, THRU 40	.118 ^{±.039} _{±.056}	.102
4,8,0	14, 16, THRU 40	.091±.039	.102

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
A		INITIAL RELEASE NUM: 70091-140		
B		(CL II) SEE ECN 27941	7-27-93 P. J. H. J.	
C		(CL II) SEE CHG NOTICE ECN: 28557	6-9-94 Prescott	



12	1		10-581821-XX3	ADAPTER	3,14
11	1		10-581819-XX1	SLEEVE	14
10	1		SEE COLUMN	GROMMET	13,14
9	1		SEE COLUMN	SLEEVE	
8	SEE NOTE 10			CONTACT	3
7	1		10-748XX-XXX	INSERT	
6	1		SEE COLUMN	CLAMP ASSY	
5	1		10-607XX-XX	GROMMET	15
4	1		10-564869-XX	SLEEVE	15
3	1		10-564867-XX3	ADAPTER	15,3
2	1		10-101379-XX1	GASKET	8
1	1		SEE COLUMN	SHELL	

SEE SHEET 2
NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS
REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.

COMPANY ID: 2
CODED/MS/CUST: Y
INTERNAL: N
LOTNO: N
DATE CODE: 9-3895
SEE PRINT: N

N/A
N/A
NEXT ASSEMBLY

UNLESS OTHERWISE SPECIFIED
LINEAR DIMENSIONS ARE IN INCHES.
TOLERANCES: .XXX±.010,
.XX ±.03, .X ±.1, ANGLES ±2°.
OTHER STANDARDS PER 9-3800
AND DOD-D-1000. NOTE REF= XX

FIND NO.	QTY REQD.	FSCM NO.	PART NUMBER	DESCRIPTION	NOTE REF.
PARTS LIST					
SPECIFICATIONS			SIGNATURES		
MATERIAL SPEC. N/A			DATES		
			PREPARED MCELLIGOTT 4/24/91		
			CHECKED: 4/22/91		
			APPROVED: 4/22/91		
			APPROVED: 5-3-91		
			1ST PART NO. 71-581453-215		
PROCESS SPEC. SEE NOTE 5			SIZE FSCM NO. D 77820 71-581440/459		
			SCALE NONE WT. REF 71-581580/599 SHEET 1 OF 2		

COMPUTER GENERATED DRAWING

000000001

TAB.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[GTC030F-24-6S](#) [GTC030F287S\(025\)](#) [GTC030F2821SLC](#) [GTC030F14S-7S](#) [GTC030F2815PLC](#) [GTC030F2815P](#)
[GTC030F-28-16PLC](#) [GTC030F14S-1S-025](#) [GTC030F22-22PX](#) [GTC030F28-84S](#) [GTC030F24-2SZ](#) [GTC030F-36-5S](#)
[GTC030F20-15S-027-LC](#) [GTC030F18-4S-A24](#) [GTC030F18-22S-B30](#) [GTC030F18-4S](#) [GTC030F20-15S](#) [GTC030F28-](#)
[17P](#) [GTC030F28-18P](#) [GTC030F16-10S](#) [GTC030F22-22P](#) [GTC030F24-10P](#) [GTC030F22-1S](#) [GTC030F28-12P-A24](#)
[GTC030F14S-7P](#) [GTC030F14S-1S](#) [GTC030F14S-1P](#) [GTC030F18-12S](#) [GTC030F14S-6P](#) [GTC030F28-15S](#)
[GTC030F20-19S](#) [GTC030F32-6S](#) [GTC030F24-9S](#) [GTC030F28-7S](#) [GTC030F28-21P](#) [GTC030F18-22S-027](#)
[GTC030F32-10S](#) [GTC030F24-5S](#) [GTC030F20-23S](#) [GTC030F20-29S](#) [GTC030F20-23P](#) [GTC030F28-17S](#)
[GTC030F28-21PZ](#) [GTC030F18-19S](#) [GTC030F24-28S](#) [GTC030F16S-8S](#) [GTC030F16-11P](#) [GTC030F24-9P](#)
[GTC030F18-22S](#) [GTC030F16-9S](#) [GTC030F14S-9S](#) [GTC030F20-3P-LC](#) [GTC030F24-28SW](#) [GTC030F36-10S-LC](#)
[GTC030F24-5P-B30](#) [GTC030F24-28SX](#) [GTC030F24-28SY](#) [GTC030F32-22P](#) [GTC030F14S-5S-A24](#) [GTC030F14S-](#)
[9P](#) [GTC030F-24-10S](#) [GTC030F18-11S\(025\)\(LC\)](#) [GTC030F-18-19P](#) [GTC030F-24-2S](#) [GTC030F28-15P\(025\)\(B30\)](#)
[GTC030F2214P](#) [GTC030F2822S](#) [GTC030F2024P](#) [GTC030F286P](#) [GTC030F3225S](#) [GTC030F2821S](#) [GTC030F242P](#)
[GTC030F1610P](#) [GTC030F2223S](#) [GTC030F-18-12SLC](#) [GTC030F32-7S](#) [GTC030F32-6P](#) [GTC030F22-7S](#)
[GTC030F28-10S](#) [GTC030F36-15S](#) [GTC030F18-17S-025](#) [GTC030F22-21S](#) [GTC030F20-29P](#) [GTC030F32-1S](#)
[GTC030F28-5S](#) [GTC030F36-77P-LC](#) [GTC030F40-AGS](#) [GTC030F36-52P](#) [GTC030F36-3S](#) [GTC030F36-3P](#)
[GTC030F40-56P-LC](#) [GTC030F14S-A7P-B30](#) [GTC030F40-57S-025](#) [GTC030F20-19P-023](#) [GTC030F20-15S-A24-C6](#)
[GTC030F28-21P-025](#) [GTC030F20-3P-027](#) [GTC030F28-21P-LC](#) [GTC030F22-22S](#) [GTC030F20-14S](#)