






INTERFACE REQUIREMENTS			
CONTACT SIZE	SHELL SIZE	X	Y ±.040
16 SHORT	10SL, 14S, 16S	.087±.039	.079
16 LONG	16 THRU 40	.260 ^{+.052} -.041	.102
12	16 THRU 40	.118 ^{+.039} -.056	.102
0, 4, 8	16 THRU 40	.091±.039	.102

A		SHEET 1 OF 2		71-586060/079	
REV.				DOCUMENT NO.	
REVISIONS					
LTR	DESCRIPTION			DATE	
A	INITIAL RELEASE				



BLACK INK STAMP "AMPHENOL", GT NUMBER, SEE COLUMN, AND DATE CODE, (9-3895), APPROX .125 HIGH, IN APPROX LOCATION SHOWN PER 9-3856-5.
EXAMPLE:
AMPHENOL GTC030G20-33P 0452

SEE SHEET 2


NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.

PRO/ENGINEER INFORMATION	
N/A	Pro/e Model Used:
N/A	GTC030G.ASSEM
Drawing Name:	
71-586060_079	

UNLESS OTHERWISE SPECIFIED
LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXXX = ±.0005 ANGLES= ±2° .XXX = ±.010 .XX = ±.03 .X = ±.1
DIM. & TOL. PER ASME Y14.5M; DRM PER MIL-DTL-31000; OTHER Amphenol Sds. PER 9-3800
LEGENDS: = FLAG NOTE CALL OUT REFERENCE ONLY

SPECIFICATIONS
MATERIAL SPEC. N/A
PROCESS SPEC. SEE NOTE 5

7	I	10-748XX-()	INSERT			
6		SEE NOTE 8	CONTACT			
5	I	10-564846-XX3	ADAPTER			
4	I	10-564869-XX	SLEEVE, COMPRESSION			
3	I	10-607XX-()	GROMMET			
2	I	10-101379-XXI	GASKET			
1	I	SEE COLUMN	SHELL			
POS	QTY	PART NUMBER	DESCRIPTION	NOTE		
PARTS LIST						
APPROVALS		DATE	AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, N.Y. 13858 CONNECTOR, ELECTRICAL RECEPTACLE, TYPE GTC030G-(), OLIVE DRAB CADMIUM PLATED			
PREPARED BY A.Prescott		12-Aug-04				
ENGINEER IN CHARGE R.Barnes						
DESIGN MANAGER D.Gallusser						
DESIGN ACTIVITY GROUP C & I						
THIRD ANGLE PROJECTION			SIZE C	CAGE CODE 77820	DOCUMENT NO. 71-586060/079	REV. A
			SCALE: 2.0		REF: 71-621380/399	SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[GTC030G2015P](#) [GTC030G2-28-11S](#) [GTC030G-28-51S](#) [GTC030G24-28P](#) [GTC030G32-17P](#) [GTC030G32-17PW](#)
[GTC030G2-24-96P](#) [GTC030G2-22-8P](#) [GTC030G18-1P-B30](#) [GTC030G28-20S-025](#) [GTC030G16-10S](#) [GTC030G22-](#)
[22P](#) [GTC030G2245P](#) [GTC030G2-28-16P](#) [GTC030G18-8S-025-A24](#) [GTC030G18-10P-025](#) [GTC030G20-18P-025](#)
[GTC030G2-28-21S-LC](#) [GTC030G18-8P-025-A24](#) [GTC030G28-21P-025-LC](#) [GTC030G20-18S-025](#) [GTC030G18-11P-](#)
[025](#) [GTC030G36-4SW](#) [GTC030G28-21P](#) [GTC030G36-4SX](#) [GTC030G2-28-21S](#) [GTC030G28-21S](#) [GTC030G32-6P-](#)
[B30](#) [GTC030G28-15S-025](#) [GTC030G28-18S](#) [GTC030G28-2S](#) [GTC030G28-AYS-RDS](#) [GTC030G32-25P](#)
[GTC030G22-12P](#) [GTC030G2-22-23S](#) [GTC030G22-23S](#) [GTC030G2-22-9P](#) [GTC030G22-2P](#) [GTC030G2-28-19S](#)
[GTC030G18-10P](#) [GTC030G18-1S](#) [GTC030G18-1S-B30](#) [GTC030G20-18P](#) [GTC030G20-18S](#) [GTC030G20-19S-RDS](#)
[GTC030G10SL-4P](#) [GTC030G14S-2S-LC](#) [GTC030G14S-5S-LC](#) [GTC030G14S-6P](#) [GTC030G14S-6P-A24](#)
[GTC030G14S-6S](#) [GTC030G18-19S](#) [GTC030G32-25S](#) [GTC030G40-80P](#) [GTC030G10SL-3P](#) [GTC030G16-10S-025](#)
[GTC030G40-57S-RDS](#)