




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2017-03-16	Frank Deng	Change Rev.01 To Rev.A
B	LEN1770176	2017-07-03	Frank Deng	Change Note



Conn.
Pin Assignments
Front View

5	Blue 藍	24#	Twist
4	White 白	24#	
3	Black 黑	22#	Twist
2	Red 紅	22#	
1	Drain 地線	22#	
Conn.	Wire Color		
Pin Out			

HPC-05BFFM-SL8AXX

XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters
Cable Length(L): 01~99Meters

- △B Note:
- * (QC) Important Dimension To Check.
 - * Waterproof Rate: IP68
In 1 meter water within 24 hours
 - * Connector: PU, Black
 - * Nut: Nylon, Black
 - * F Pin: Copper Alloy, Gold Plated 30u"
 - * Outer Mold: PU, Blue
 - * Cable: CL2, (24#*1P+A/M)+(22#*1P+A/M)+
D+B,PVC UV Cable, OD=6.7mm, Black
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TOLERANCE		±0.5mm		TITLE		NMEA 2000 SINGLE ENDED CABLE MICRO-C, F CONN F PIN, PLASTIC		Amphenol LTW		安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY		DATE	
						SCALE		Free		A4		SHEET		1		OF		1	
						REV.		B		WC-REV.		A.1		(QC): Inspection item		DWG NO		HPC-05BFFM-SL8AXX	
																CUSTOMER		ALTW	
																CHECKED BY		Fisher Wang	
																APPROVED BY		Kevin Hu	
																		2017-07-06	
																		2017-07-06	
																		2017-07-06	
																		2017-07-06	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HPC-05BFFM-SL8A01](#)