






REV	ECN	APP'D
-	7567	5/15/15



- NOTES:
- MATERIALS:
HOUSING: POLYETHERIMIDE PER ASTM-D5205
GROMMET: SILICONE RUBBER PER A-A-59588
THREADED INSERT: STAINLESS STEEL
 - OPERATING RANGE:
TEMPERATURE: -65 °C TO 125 °C
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS AT SEA LEVEL AND 500 VRMS AT 80,000 FT. ALTITUDE
VIBRATION: MIL-STD-202, METHOD 204, TEST CONDITION G
SHOCK: MIL-STD-202, METHOD 213, TEST CONDITION C
 - PART ACCEPTS M39029/101-554 AND M39029/92-552 SOCKET CONTACTS, SIZE 16/16 AND SIZE 22/22.

APCD P/N	HARDWARE PACKAGE	CONTACTS SUPPLIED
JRE100100	NONE	NONE
JRE100101	NONE	YES
JRE100110	YES	NONE
JRE100111	YES	YES

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd SPECIFICATION DRAWING			
ANSI Y14.5M UNITS: INCHES Pro/E FILE	.XX ±0.01 .XXX ±0.005 ANGLES ±0.5°		ENGR W. HEDBERG 7/28/15	TITLE QUICK MOUNT RELAY SOCKET 1 POLE REF: M12883/56-01		
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA	CHKD <i>William Lane</i> 8/4/15	SIZE B	DWG NO. JRE100100_C	REV -	
		APPD <i>Stanley</i> 8/5/15	CODE: 58982	SCALE: 2:1	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[JRE200110](#) [JRE200111](#) [JRE200101](#) [JRE100100](#)