




04	2x2 CONTACTS	0	Black	RoHS
06	2x3 CONTACTS	5	Green	Pb<40,000ppm
...	...	6	Blue	
48	2x24 CONTACTS	8	Grey	

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YL-5.08mm Series “-” Left					
PART NO.		YLxx41x0xxxxG		DWG NO.		8YL0101	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacke 2009.03.25	Jacke 2009.03.25		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
					REV.: E	X.XX	±0.10
				SHEET: 01/01		X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>YL0441500000G</u>	<u>YL0641500000G</u>	<u>YL0841500000G</u>	<u>YL1041500000G</u>	<u>YL1241500000G</u>	<u>YL1441500000G</u>
<u>YL1641500000G</u>	<u>YL1841500000G</u>	<u>YL2041500000G</u>	<u>YL2241500000G</u>	<u>YL2441500000G</u>	<u>YL2641500000G</u>
<u>YL2841500000G</u>	<u>YL3041500000G</u>	<u>YL3241500000G</u>	<u>YL3441500000G</u>	<u>YL3641500000G</u>	<u>YL3841500000G</u>
<u>YL4041500000G</u>	<u>YL4241500000G</u>	<u>YL4441500000G</u>	<u>YL4641500000G</u>	<u>YL4841500000G</u>	