




1		2		3		4		5		6		7		8			
								REV. A		ECN NO. Initial Release		DATE 2008/05/06		SIGN Rex		DESCRIPTION Rev.01 Change To A	
								B		LEN-930466		2009/03/04		ZhaoRongFu		Add Waterproof Rate	

Notes:


- \* **QC** Important Dimension To Check
- \* **Waterproof Rate: IP67**
- \* LED Holder: Copper Alloy, Nickel Plating
- \* LED Spec:
  - ø3mm, Super Bright, Red/Green, Bi-Color LED
  - Lens Color: Water Clear
  - Forward Voltage: Red Typ. 2.05V  
Green Typ. 3.4V
  - Forward Current: Red Typ. 35mA  
Green Typ. 20mA
  - Luminous Intensity: Red Typ. 1000(Mcd)  
Green Typ. 2000(Mcd)
  - Reverse Voltage: DC 5V
  - Operating Temperature: -30~+80°C
- \* O-Ring: Silicone, Gray
- \* Screw Nut: Copper Alloy, Nickel Plating
- \* For Panel Thickness 6.5 max.

Recommended Panel Cut-Out





① LED



② LED Holder

③ Liquid Glue

④ O-Ring

⑤ Nut

⑥ Shrink Tube

⑦ Shrink Tube

+ Red

+ Green

QC M8\*1.0

QC 6.90

ALTW  
CONFIDENTIAL  
2009.03.04  
R&D DEPT.

ALTW  
DCC. DEPT.  
CONFIDENTIAL  
2009.03.12  
ISSUED

UNIT:mm		TITLE Waterproof Led (ø3mm) Red/Green, Solder Type		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO L08-01AAAS-MR7001		DRAWN BY Zhao Rong Fu		DATE 2009/03/04	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE Free		SHEET 1 OF 1		DWG NO L08-01AAAS-MR7001		CHECKED BY Prune		DATE 2009/03/05	
REV. B		SIZE A4		QC : Inspection Item		CUSTOMER ALTW		APPROVED BY LUKE		DATE 2009/03/05	

1

2

3

4

5

6

7

8

FWI0702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[L08-01AAAS-MR7001](#)