



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN-8B0711	2008/11/24	TOMMY CHANGE	THE NOTE
D	LEN-930476	2009/03/04	ZhaoRongFu	Add Waterproof Rate
E	LEN1810174	2018/01/08	Mark	Change Note & Shrink Tube

- Notes:
- * $\varnothing$ Important Dimension To Check
 - * Waterproof Rate: IP67
 - * LED Spec.
 - $\varnothing$ 5 mm, Red
 - Lens Color: Water Clear
 - Viewing Angle: 30°
 - Absolute Maximum Rating (@25°C);
 - * Power Dissipation: 100mW
 - * Forward Current(IF): 30mA
 - * Reverse Voltage(VR): 5V
 - Forward Voltage (VF): typ. 2.2V (@IF=20mA, 25°C)
 - Luminous Intensity (IV): typ. 5000mcd (@IF=20mA, 25°C)
 - * Internal Current Limiting Resistor: 91 Ω
 - * Recommended Operating Voltage: DC 4V
 - * LED Holder: Copper Alloy, Nickel Plating
 - * O-Ring: EPDM, Black
 - * Screw Nut: Copper Alloy, Nickel Plating
 - * Operating Temperature: -40~+80°C
 - * Panel Thickness: 6.5mm max.



UNIT: mm		TITLE Waterproof Led ($\varnothing$ 5mm) Red, Solder Type		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO L08-01RBAS-MR7001	DRAWN BY Mark	DATE 2018/01/08
TOLERANCE .X $\pm$ 0.25 .XX $\pm$ 0.1 .XXX $\pm$ 0.05 ANGLES $\pm$ 1°		SCALE 2:1	SIZE A4	SHEET 1 OF 2		DWG NO L08-01RBAS-MR7001	CHECKED BY Neo	DATE 2018/01/08
REV. E		WC-REV. A.2	$\varnothing$ Inspection item			CUSTOMER ALTW	APPROVED BY Max	DATE 2018/01/08

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[L08-01RBAS-MR7001](#)