








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2012/10/22	Ruru	LC20-03RMFS-SS8001 To LC20-03PMFS-SN8001
B	LE31650231	2016/05/04	Vicky	Update Note





- ④ Screw Nut
③ Tooth Washer
② Gasket



Recommend Panel Cut-Out

Assembly Instruction



- Note:**
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP68
IP68: 1M depth of water in 24 Hrs.
(防水等級: IP68)
IP68: 水深一米測試 24 小時
 - * Shell: Zinc Alloy#3, Ni Plated, Silver.
 - * Insulation: Nylon, Black
 - * Female Pin: Copper Alloy, Silver Plated
 - * Gasket: Silicone, Gray
 - * Recommended Panel Thickness 5.0mm(Max).

UNIT: mm		TITLE	
TOLERANCE		PANEL NUT 3PIN M CONN F PIN	
.X	± 0.25	SCALE	1:1
.XX	± 0.1	SIZE	A4
.XXX	± 0.05	SHEET	1 OF 1
ANGLES	$\pm 1^\circ$	REV.	B
		WC-REV.	A.2
		QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	LC20-03PMFS-SN8001	DRAWN BY	Vicky	DATE	2016-05-04
DWG NO	LC20-03PMFS-SN8001	CHECKED BY	Rita	DATE	2016-05-04
CUSTOMER	ALTW	APPROVED BY	Lisa	DATE	2016-05-04

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LC20-03PMFS-SN8001](#)