









REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2012/10/22	Ruru	LD20-10PMFS-SS8001 To LD20-10PMFS-SN8001
B	LE31650233	2016/05/04	Vicky	Update Note



Recommend Panel Cut-Out

Assembly Instruction



Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP68
IP68: 1M depth of water in 24 Hrs.
(防水等級: IP68)
IP68: 水深一米測試 24 小時
- * Shell: Zinc Alloy#3, Ni Plated, Silver.
- * Insulation: Nylon, Black
- * Female Pin: Copper Alloy, Silver Plated
- * Gasket: Silicone, Gray
- * Recommended Panel Thickness 5.0mm(Max).

UNIT: mm		TITLE		Amphenol LTW		ITEM NO	DRAWN BY	DATE
		PANEL NUT 10PIN M CONN F PIN		安費諾亮泰企業股份有限公司		LD20-10PMFS-SN8001	Vicky	2016-05-04
TOLERANCE		SCALE	SIZE	SHEET	OF	DWG NO	CHECKED BY	DATE
.X ±0.25		1:1	A4	1	1	LD20-10PMFS-SN8001	Rita	2016-05-04
.XX ±0.1		REV.	WC-REV.	QC: Inspection item		CUSTOMER	APPROVED BY	DATE
.XXX ±0.05		B	A.2			ALTW	Lisa	2016-05-04
ANGLES ±1°								

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LD20-10PMFS-SN8001](#)