









REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2012/10/22	Ruru	LD20-10PMFS-SS8001 To LD20-10PMFS-SW8001
B	LE31650234	2016/05/04	Vicky	Update Note



△ Note:

- * ⌀ Important Dimension.
- * Waterproof Rate: IP68.
IP68: 1M depth of water in 24 Hrs.
(防水等級: IP68)
IP68: 水深一米測試 24 小時
- * Shell: Zinc Alloy#3 ,Ni Plated ,Silver.
- * Insulation: Nylon ,Black.
- * Female Pin: Copper Alloy , Silver Plated.
- * Gasket: Silicone ,Gray.
- * Screw: Stainless Steel.
- * Recommended Panel Thickness 9mm(Max).

UNIT:mm		TITLE	
		PANEL SCREW 10PIN M CONN F PIN	
TOLERANCE		SCALE	SIZE
.X ±0.25		1:1	A4
.XX ±0.1			
.XXX ±0.05		REV.	WC-REV.
ANGLES ±1°		B	A.2
		QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	LD20-10PMFS-SW8001	DRAWN BY	Vicky	DATE	2016-05-04
DWG NO	LD20-10PMFS-SW8001	CHECKED BY	Rita	DATE	2016-05-04
CUSTOMER	ALTW	APPROVED BY	Lisa	DATE	2016-05-04

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LD20-10PMFS-SW8001](#)