









REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2012/10/22	Ruru	LD20-12RMFS-SS8001 To LD20-12PMFS-SN8001
B	LE31650235	2016/05/04	Vicky	Update Note



Assembly Instruction



Recommend Panel Cut-Out



△ Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP68
IP68: 1M depth of water in 24 Hrs.
(防水等級: IP68)
IP68: 水深一米測試 24 小時
- * Shell: Zinc Alloy#3, Ni Plated, Silver.
- * Insulation: Nylon, Black
- * Female Pin: Copper Alloy, Silver Plated
- * Gasket: Silicone, Gray
- * Recommended Panel Thickness 5.0mm(Max).

UNIT:mm		TITLE
TOLERANCE		PANEL NUT 12PIN M CONN F PIN
.X	±0.25	SCALE
.XX	±0.1	1:1
.XXX	±0.05	SIZE
ANGLES	±1°	A4
		SHEET
		OF
		REV.
		B
		WC-REV.
		A.2
		$\varnothing$ Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	LD20-12PMFS-SN8001	DRAWN BY	Vicky	DATE	2016-05-04
DWG NO	LD20-12PMFS-SN8001	CHECKED BY	Rita	DATE	2016-05-04
CUSTOMER	ALTW	APPROVED BY	Lisa	DATE	2016-05-04

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LD20-12PMFS-SN8001](#)