






REV.	ECN NO.	DATE	SIGN	DESCRIPTION

360° Adjustable Key Code Direction



Pin Assignments
Front View



Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Nut: PBT+PC, Black.
- * Male Nut: Zinc Alloy, Nickel Plated.
- * O-Ring: Silicon, Grey.
- * Clamp Ring: Nylon, Black.
- * Sealing Nut: PBT+PC, Black.
- * Seal: Silicon, Grey.
- * Seal For Cable OD: $\varnothing 4.0\text{mm} \sim \varnothing 7.0\text{mm}$.
- * Applicable Wire gauge (Stranded wire cross section)
26AWG ~24AWG
- * Mating Recommended tightening torque:
3~4 kgf.cm / 0.29~0.39 N.m
- * Sealing-Nut Recommended tightening torque:
4~6 kgf.cm / 0.39~0.59 N.m
- * Detailed applicable wire specifications may vary depending on the actual wire construction.

UNIT:mm		TITLE		ITEM NO		DRAWN BY		DATE	
		MI2A Unshielded Assy 90° 10Pin M Conn. M Pin		MI2A-10BMMA-SR7001		Yulong_wang		2015-05-04	
TOLERANCE		SCALE		DWG NO		CHECKED BY		DATE	
.X ±0.25		1:1		MI2A-10BMMA-SR7001		Lu Di		2015-05-04	
.XX ±0.1		SIZE		CUSTOMER		APPROVED BY		DATE	
.XXX ±0.05		A4		ALTW		Jerry		2015-05-04	
ANGLES ±1°		REV.							
		A							
		WC-REV.							
		A.2							
		QC: Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M12A-10BMMA-SR7001](#)