








		2	3	4	5	6	7	8																			
F	E	 Recommended Panel Cut-Out		REV.		ECN NO.	DATE	SIGN	DESCRIPTION																		
				B		LEN1741194~97	2017/04/11	Jinhai	Add The Size Table																		
				C		C200275	2020/03/12	Nan_Su	△C*1																		
D	C																										
B	A	<table><tr><td>MI2A-03PMMR-SF7003</td><td>25.9</td><td>24.8</td><td>1.0</td></tr><tr><td>MI2A-04PMMR-SF7003</td><td>25.9</td><td>24.8</td><td>1.0</td></tr><tr><td>MI2A-05PMMR-SF7003</td><td>25.9</td><td>24.8</td><td>1.0</td></tr><tr><td>MI2A-08PMMR-SF7003</td><td>25.7</td><td>25.0</td><td>0.8</td></tr><tr><td>Item No.</td><td>A</td><td>B</td><td>OD</td></tr></table>		MI2A-03PMMR-SF7003	25.9	24.8	1.0	MI2A-04PMMR-SF7003	25.9	24.8	1.0	MI2A-05PMMR-SF7003	25.9	24.8	1.0	MI2A-08PMMR-SF7003	25.7	25.0	0.8	Item No.	A	B	OD			Note: *  Important Dimension To Check. * Waterproof Rating: IP67(Mated Waterproof) * Connector: PBT+PC, Black * Male Pins: Copper Alloy, Gold Plated * Shell: Zinc Alloy, Nickel Plated * Nut: Zinc Alloy, Nickel Plated * O-Ring1: Silicone, Black * O-Ring2: Silicone, Gray * Pin Holder: PBT+PC, Black * Rated Voltage: 3 & 4Pin 250V dc. or ac. 5Pin 60V dc. or ac. 8Pin 30V dc. or ac. * Rated Current: 3~5Pin 4A 8Pin 2A * For Panel Thickness Max. 3.0mm * For PCB Thickness Max. 1.6mm	
MI2A-03PMMR-SF7003	25.9	24.8	1.0																								
MI2A-04PMMR-SF7003	25.9	24.8	1.0																								
MI2A-05PMMR-SF7003	25.9	24.8	1.0																								
MI2A-08PMMR-SF7003	25.7	25.0	0.8																								
Item No.	A	B	OD																								
 Pin Assignment Front View																											
UNIT:mm  		TITLE MI2, 90° Panel M Conn. M Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO. MI2A-XXPMMR-SF7003		DRAWN BY Jinhai	DATE 2017-04-11																		
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 3:2 SIZE A4 SHEET 1 OF 2 REV. C WC-REV. A.3  :Inspection item				DWG NO. MI2A-XXPMMR-SF7003		CHECKED BY Feng-li	DATE 2017-04-11																		
						CUSTOMER ALTW		APPROVED BY Jerry	DATE 2017-04-11																		
								W10814-03-0001A2																			

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

F		2		3		4		5		6		7		8			
		M 12A - XX P M M R - S F 7 003															
		12A: A-Code										003: M12*1.0					
E		03: 3Pin										7: IP67 (防水等級67)					
		04: 4Pin															
		05: 5Pin															
		08: 8Pin															
		P: Panel (板端)															
		M: Male Connector (公座)															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M12A-03PMMR-SF7003](#)