





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1580033~034	2015/07/26	Yulong_wang	Change to Share Drawing.
C	LEN1690056~057	2016/09/05	Yulong_wang	Add 3, 4 Pin & IP69K.



Legend for connector code: M 12B - XX P M M S - S F 8 XXX

12B: B-Code

03: 3Pin

04: 4Pin

05: 5Pin

P: Panel (板端)

M: Male Connector (公座)

M: Male Pin (公Pin)

001: PG9



002: M16*1.5

8: IP68/69K (防水等級68/69K)

F: Front Fasten (前鎖式/Enclosure Rear Mount)

S: Screw (螺紋式)

S: Solder Type (焊接式)



Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP68, IP69K.
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Shield: Zinc Alloy, Nickel Plated.
- * Screw Nut: Zinc Alloy, Nickel Plated.
- * Panel O-Ring: Viton, Black.
- * Rated Voltage: 3 & 4Pin 250V dc. or ac. 5Pin 60V dc. or ac.
- * Rated Current: 4A
- * Operating Temperature: -40~+105°C
- * For Panel Thickness Max 4.5mm.
- * Recommended Nut Torque: 4-6 Kgf.cm.

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
.X ±0.25		.XX ±0.1		M12 B-Code Male Conn.		DWG NO		Yulong_wang		2016-09-05	
.XXX ±0.05		ANGLES ±1°		Solder Front Type		M12B-XXPMMS-SF8XXX		CHECKED BY		Jinhai	
SCALE 2:1		SIZE A4		SHEET 1 OF 1		CUSTOMER		APPROVED BY		Jerry	
REV. C		WC-REV. A.5		$\varnothing$ Inspection item		ALTW				2016-09-05	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M12B-05PMMS-SF8001](#) [M12B-05PMMS-SF8002](#)