




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2015/09/07	Cary	Change Rev. 01 to Rev.A
B	LE317A0020	2017/10/15	Feng_Li	Update The Note
C	CI91643	2019/09/20	Vicky	Update Wire Tolerance

MI2T-04PMMS-SF8CXX/C


15:150mm
20:200mm
95:950mm
Cable Pitch Unit:50mm

A0:1000mm
A5:1500mm
Cable Pitch Unit:100mm
Wire Length(L):150~1500mm




Note:

- * \varnothing Important Dimension.
- * Waterproof Rate:IP68.
- * IP68: 1M Depth Of Water In 24hours.
- * \triangle Housing:Nylon+GF,UL94V-0,Black.
- * Male Pin:Copper Alloy,Gold Plated.
- * Shield:Zinc Alloy,Nickel Plated.
- * Panel Nut:Zinc Alloy,Nickel Plated.
- * O-Ring: Viton,Black.
- * Wire Harness: UL1015 16AWG(1.5mm²).
- * Rated Voltage: 60V DC.
- * Rated Current at 40°C: 12A
- * Operation Temperature: -40~85°C.
- * For Panel Thickness Max 4.5mm.
- * Nut Torque:4-6 Kgf.cm(0.4~0.6N.m).
- * Wire harness Tolerance: 150~300 ±15mm
301~1000 ±20mm
 \triangle Over1000 +50/-0mm



Pin Assignment
Front View



Recommended
Panel Cut-Out

4	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

UNIT:mm	
TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

TITLE MI2 T-Code 4Pin Male Type			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. C	WC-REV. A.2	\varnothing Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2019-09-20
DWG NO MI2T-04PMMS-SF8CXX	CHECKED BY Rita	DATE 2019-09-20
CUSTOMER ALTW	APPROVED BY Max	DATE 2019-09-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M12T-04PMMS-SF8C15](#)