


M39012/58-3006



NOTES:

- 1.) MATING END DIM'S PER MD-107.
- 2.) PKG. PARTS 3 THRU 8 LOOSE WITH CONNECTOR.

DESIGN CONTROLLED 39012

SYM	DESCRIPTION	DATE	APPR.	UNLESS OTHERWISE SPECIFIED	SOLITRON/MICROWAVE		REF.
E	REL. DCNF-10262	2/86	D	1. REMOVE ALL BURRS	PORT SALERNO, FLORIDA		
A	REV. DCN. 20666	4-93	DW	2. BREAK ALL CORNERS & EDGES .005 R MAX.	MATERIAL		TITLE
				3. CHAMFER 1ST & LAST THREADS 45°			SMA 4 HOLE FLANGE
				4. SURFACE ROUGHNESS 63 ✓ MIL-STD-10	FINISH		MT. JACK RECEPTACLE
				5. DIAMETERS ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R.			FOR RG 178/U CABLE.
				6. ALL DIMENSIONS ARE AFTER PLATING			
				DIMENSIONS ARE IN INCHES			
				TOLERANCES			
				DECIMALS	FRACTIONAL	ANGULAR	
				.X ± .030		X' ± 1°	
				.XX ± .015	± 1/64	X'X ± 15'	
				.XXX ± .005			
				DRAWN <u>T.</u>	DATE 12-23-85	SCALE	DRAWING NO.
				CHECKED	DATE	6X	M39012/58-3006
				APPROVED <u>D</u>	DATE 2-26-86	CODE IDENT. NO.	SHT. 2 OF 2
						95077	
						A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M39012/58-3006](#)