

1		2		3		4		5		6		7		8									
ALTW CONFIDENTIAL 2018-04-11 R&D DEPT. ALTW DCC. DEPT. CONFIDENTIAL 2018.06.20 ISSUED 比例 3:1 Pin Assignments Front View <table><tr><td>4</td><td>Black 黑</td></tr><tr><td>3</td><td>Blue 藍</td></tr><tr><td>1</td><td>Brown 棕</td></tr><tr><td colspan="2">Conn. Wire Color</td></tr><tr><td colspan="2">Pin Out</td></tr></table>				4	Black 黑	3	Blue 藍	1	Brown 棕	Conn. Wire Color		Pin Out		REV.		ECN NO.		DATE		SIGN		DESCRIPTION	
				4	Black 黑																		
				3	Blue 藍																		
1	Brown 棕																						
Conn. Wire Color																							
Pin Out																							
A				2018/04/11		Chingmei		New Release															

Amphenol

26.5

23.6

10.5

9.0

4.6

L (mm)

①

M8AS-03BMMM-SR7000

②

Cable

M8*1.0

Conn.

M8AS-03BMMM-SR7AXX

(Cable Length)

XX: 01~99Meters

01: 01Meter

02: 02Meters

:

:

99: 99Meters

Note:

* ①Important Dimension

* Waterproof Rate: IP67

* Connector: Nylon, Black

* Pin: Copper Alloy, Gold Plated

* Screw Nut: Zinc Alloy, Nickel Plated

* Cable: 3C*24#+AL/MY+B,
PVC Jacket, Black

* Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm

UNIT:mm

TOLERANCE

±0.5mm

TITLE

G8 SHIELD CONN WITH KEY
CABLE SCREW 3PIN M CONN M PIN

SCALE

2:1

SIZE

A4

SHEET

1

OF

1

REV.

A

WC-REV.

A.5

①

Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

M8AS-03BMMM-SR7AXX

DWG NO

M8AS-03BMMM-SR7AXX

CUSTOMER

ALTW

DRAWN BY

Chingmei

CHECKED BY

Neo

APPROVED BY

Max

DATE

2018/04/11

DATE

2018/04/11

DATE

2018/04/11

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M8AS-03BMMM-SR7A01](#) [M8AS-03BMMM-SR7D01](#)