




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2018/04/11	Chingmei	New Release



比例 3:1

Pin Assignments
Front View

4	Black 黑
3	Blue 藍
1	Brown 棕
Conn.	Wire Color
Pin Out	

M8S-03BFFM-SL7AXX

↓
(Cable Length)
XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters

- Note:
- * (QC) Important Dimension
 - * Waterproof Rate: IP67
 - * Connector: Nylon, Black
 - * Pin: Copper Alloy, Gold Plated
 - * Screw Nut: Zinc Alloy, Nickel Plated
 - * O-Ring: Silicon, Gray
 - * Cable: 3C*24#+AL/MY+B, PVC Jacket, Black
 - * Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
31~99M: ±500mm

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
±0.5mm				M8 SHIELD CONN WITH KEY CABLE SCREW 3PIN F CONN F PIN		M8S-03BFFM-SL7AXX		Chingmei		2018/04/11	
				SCALE 2:1		DWG NO		CHECKED BY		DATE	
				SIZE A4		M8S-03BFFM-SL7AXX		Neo		2018/04/11	
				SHEET 1 OF 1		CUSTOMER		APPROVED BY		DATE	
				REV. A		ALTW		Max		2018/04/11	
				WC-REV. A.5							
				(QC) Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M8S-03BFFM-SL7A01](#) [M8S-03BFFM-SL7D01](#)