



Pin Assignments Front View

4	Black 黑
3	Blue 藍
1	Brown 棕
Conn.	Wire Color
Pin Out	



Conn.

M8S-03BMMM-SR7Axx

```

↓
(Cable Length)
XX: 01~99Meters
01: 01Meter
02: 02Meters
    :
    :
99: 99Meters

```

Note:

- *  Important Dimension
- * Waterproof Rate: IP67
- * Connector: Nylon, Black
- * Pin: Copper Alloy, Gold Plated
- * Screw Nut: Zinc Alloy, Nickel Plated
- * Cable: 3C*24#+AL/MY+B,
PVC Jacket, Black, OD=5
- * Cable Length Tolerance: 01M: $\pm 40\text{mm}$
02~05M: $\pm 60\text{mm}$
06~10M: $\pm 100\text{mm}$
11~30M: $\pm 200\text{mm}$
31~99M: $\pm 500\text{mm}$

UNIT: mm	
TOLERANCE	
$\pm 0.5\text{mm}$	

TITLE	
M8 SHIELD CONN WITH KEY	
CABLE SCREW 3PIN M CONN M PIN	

SCALE 2:1	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV. A.5	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	M8S-03BMMM-SR7AXX	DRAWN BY	Chingmei	DATE	2018/04/11
DWG NO	M8S-03BMMM-SR7AXX	CHECKED BY	Neo	DATE	2018/04/11
CUSTOMER	ALTW	APPROVED BY	Max	DATE	2018/04/11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M8S-03BMMM-SR7A01](#) [M8S-03BMMM-SR7D01](#)