




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1660367~72	2016/05/30	Jinhai	Change Logo

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



- Note:
- * **QC** Important Dimension.
 - * Waterproof Rate: IP68
 - * Connector: Polyurethane (PU), Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Cable: Black,(24#*1P+A)+(22#*1P+A)+Drain+AL.Mylar+Braid
PVC UV Cable OD=6.0mm
 - * Cable Length Tolerance:1M~10M±5%mm,11M~99M±500mm.

5	Blue (24AWG)	5	Twist
4	White (24AWG)	4	
3	Black (22AWG)	3	Twist
2	Red (22AWG)	2	
1	Drain (22AWG)	1	
Conn.1	Wire Color	Conn.2	
Pin Out			

UNIT:mm	
TOLERANCE	
±0.5 mm	

TITLE			
M12P Conn NMEA I Adapt Screw FF Conn FF Pin			
SCALE	Free	SHEET	1 OF 1
REV. B	SIZE A4	QC :Inspection Item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Jinhai	2016/05/30
DWG NO	CHECKED BY	DATE
MC-000505-OFF-CSAXX	Tom	2016/05/30
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2016/05/30

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MC-000505-OFF-CSA01](#) [MC-000505-OFF-CSA02](#) [MC-000505-OFF-CSA03](#) [MC-000505-OFF-CSA04](#) [MC-000505-](#)
[OFF-CSA05](#) [MC-000505-OFF-CSA10](#)