




5		6		7		8	
REV.	ECN NO.	DATE	SIGN	DESCRIPTION			
B	LE3-030073~76	2010/02/22	Tina	Change to Conn.			
C	LEN1670059~062	2016/06/30	Vicky	Update Logo			



Note:

- * **QC** Important Dimension.
- * Waterproof Rate: IP68
IP68: 1M Depth Of Water In 24hours
- * Connector: Polyurethane (PU), Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: (22AWG*1P+Al)+(18AWG*1P+Al)
+Drain+Al.Mylar+Braid, OD=7.0mm
- * Cable Length Tolerance: 1M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



5	Blue 藍	(22AWG)	Twist 對線
4	White 白	(22AWG)	
3	Black 黑	(18AWG)	Twist 對線
2	Red 紅	(18AWG)	
1	Drain 地線	(22AWG)	
Conn.	Wire Color		
	Pin Out		

Cable Length(L):01~99Meters

XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters

XX:01~99Meters
01:01Meter
02:02Meters

01:01Meter

02:02Meters

-
-
-
-

99:99Meters

Amphenol LTW

安費諾亮泰企業股份有限公司

UNIT:mm		TITLE M12P Conn NMEA Cable Screw 5Pin M Conn M Pin		Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO	DRAWN BY Vicky	DATE 2016/06/30
TOLERANCE ±0.5 mm		SCALE Free	SHEET 1 OF 1		DWG NO MCP-05BMMM-SL8BXX	CHECKED BY Rita	DATE 2016/06/30
REV. C	SIZE A4	QC :Inspection Item			CUSTOMER ALTW	APPROVED BY Lisa	DATE 2016/06/30

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MCP-05BMMM-SL8B01](#) [MCP-05BMMM-SL8B10](#) [MCP-05BMMM-SL8B05](#) [MCP-05BMMM-SL8B02](#)