





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3I350I2I~I24	20I3/05/I4	Vicky	Modify Note & Wire Color.
C	LE3I520I39~I42	20I5/02/05	Vicky	Update Logo
D	LENI5A0274~277	20I5/I0/I3	Vicky	Update Pin Out



Note:

- * $\varnothing$ Important Dimension
- * Waterproof Rate: IP68
IP68: IM Depth Of Water In 24hours
- * Connector: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Wire Harness: ULI007
- * Cable: UL20276 [(18#*IP+AL0+(16#*IP+AL)]+D+AL+B,
PVC Jacket, UV Resistant, Black, OD10.0mm
- * Cable Lenght Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



MN-050500-FM0-TSCXX
XX: 01~99Meters
01: 01Meters
02: 02Meters
...
99: 99Meters
Cable Length(L): 01~99Meters

Blue (18AWG) 藍	5	5	Blue (18AWG) 藍
White (18AWG) 白	4	4	White (18AWG) 白
Black (16AWG) 黑	3	3	Black (16AWG) 黑
Red (16AWG) 紅	2	2	Red (16AWG) 紅
Green (18AWG) 綠	1	1	Drain (18AWG) 地線
Wire Color $\triangle$	Conn.1	Conn.2	Cable $\triangle$
Pin Out			

UNIT:mm
TOLERANCE
±0.5 mm

TITLE Mini T-Cable Screw FM Conn FM Pin To Cable			
SCALE 3:4	SIZE A4	SHEET 1 OF 1	
REV. D	WC-REV. A.2	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2015-10-13
DWG NO MN-050500-FM0-TSCXX	CHECKED BY Rita	DATE 2015-10-13
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015-10-13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MN-050500-FM0-TSC10](#) [MN-050500-FM0-TSC01](#) [MN-050500-FM0-TSC02](#) [MN-050500-FM0-TSC05](#)