




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1160182~185	2011/06/22	Vicky	REF. TO ECR/N.NOTE.
C	LEN1670630~633	2016/07/18	Vicky	Update Logo



△ MN-05AMMM-SL8CXX
 XX:01~99Meters
 01:01Meter
 02:02Meters
 :
 :
 99:99Meters
 Cable Length(L):01~99Meters



Pin Assignments
Front View



Blue (18AWG)	藍	5
White (18AWG)	白	4
Black (16AWG)	黑	3
Red (16AWG)	紅	2
Drain	地線	1
Wire Color	Conn.	
Pin Out		

- Note:
- * @C Important Dimension
 - △ * Waterproof Rate: IP68
IP68: 1M Depth Of Water In 24hours
 - * Connector: PU, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Nut: Zinc Alloy, Nickel Plated
 - * Cable:UL20276[(18#*1P+Al)+(16#*1P+Al)]+D+Al+B, PVC Jacket,UV Resistant,Black,OD=10.0mm.
 - △ * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	NMEA Mini M Conn M Pin For Cable
REV. C	SCALE Free	SHEET 1 OF 1
SIZE A4	@C :Inspection Item	

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2016/07/18
DWG NO MN-05AMMM-SL8CXX	CHECKED BY Rita	DATE 2016/07/18
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2016/07/18

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MN-05AMMM-SL8C02](#) [MN-05AMMM-SL8C01](#) [MN-05AMMM-SL8C05](#) [MN-05AMMM-SL8C10](#)