



REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
A1	-	FIRST RELEASE	May/27/2017	To d TOMMY
A2	-	Modify the current rating	Jul/10/2017	White TOMMY



P/N	CONTACT PLATING(MATING AREA)
MP10B23T	TIN PLATING OVER NICKEL.
MP10B23S	SILVER PLATING OVER NICKEL.
MP10B23F	GOLD FLASH PLATING OVER NICKEL.
MP10B23G5	5µ" GOLD PLATING OVER NICKEL.
MP10B23G10	10µ" GOLD PLATING OVER NICKEL.
MP10B23G15	15µ" GOLD PLATING OVER NICKEL.
MP10B23G30	30µ" GOLD PLATING OVER NICKEL.

- NOTES : (UNLESS OTHERWISE SPECIFIED)
1. MATERIAL :
- 1.1. CONTACT BODY : COPPER ALLOY.
- 1.2. POSITIONING CLIP : COPPER ALLOY.
2. SPECIFICATIONS :
- 2.1 CURRENT RATING : 35A(MAX).
- 2.2 TERMINATION TYPE : CRIMPING.
- 2.3 WIRE RANGE : 10~12 AWG.
3. SUITABLE SOCKET : MS10B23xx.
4. ROHS COMPLIANT.
5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED			
1) All dimensions are in millimeters.			
2) Tolerances are as follows:			
1 Pt. DEC 40.30 Fractions ±1/64			
3 Pt. DEC 40.08 Angles ±1°			
3) Note reference = 			
MATERIAL SPECIFICATIONS:		CUSTOMER:	
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLEMENTARY TO THE DRAWING OF THE PART IT REPRESENTS. IT DOES NOT CONTAIN ALL DIMENSIONS AND FEATURES. SPECIFICATIONS AND PERFORMANCE DATA OF REPRODUCTION ARE LIMITED. ALL MANUFACTURING VARIATIONS.	
NEXT ASSY:		ECO-MATE PIN CONTACT MACHINE, MALE, CONTACT 2.5mm	
SCALE		SIZE TYPE DWG NO.	
NONE		B C- MP10B23xx	
SHEET		REVISION	
1		A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MP10B23G5](#) [MP10B23T](#) [MP10B23S](#) [MP10B23G15](#) [MP10B23F](#) [MP10B23G10](#) [MP10B23G30](#)