


PRODUCT DATA DRAWING

**MATERIAL**

CONNECTORS: SMA R/A Male (2912-61001)
2.92mm Bulkhead Female (SF1521-60025)

CABLE: Ø.085 Flexible Coax

SHRINK TUBING: M23053/5

PERFORMANCE

IMPEDANCE: 50 Ohms

FREQ. RANGE: DC to 18 GHz

VSWR: 1.3:1 Max, DC to 18.0 GHz
1.5:1 Max, 18.0 + GHz

INSERTION LOSS: 1.30 dB Max

NOTES

1. See individual data drawings for connector specifications
2. Dimensions shown are in inches



TITLE:

SMA R/A Male to 2.92mm Bulkhead Female 12" Cable
Assembly for Ø.085 Flexible Coax

DWG. NO.

MRSMA-085-FB292-120

DRAWN

2022-10-18 14:45:19

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MRSMA-085-FB292-120](#)