



SUITABLE FOR 1403 LAYOUT WITHOUT END CAP
CONNECTOR CONFIGURATION



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPROVED
A1	-	RELEASED DRAWING	Jan-17-2018	Nick	TOMMY
A2	-	UPDATE DRAWING	Jan-19-2018	Nick	TOMMY
A3	-	UPDATE DRAWING	Aug-06-2019	Ronald	Tommy
A4	-	Add the note	Sep-14-21	Flan	Tommy



1. MATERIAL:

- 1.1. CONTACT BODY: COPPER ALLOY.
1.2. POSITIONING CLIP: COPPER ALLOY.

2. SPECIFICATIONS:

- 2.1 CURRENT RATING: 45A(MAX).
2.2 TERMINATION TYPE: CRIMPING.
2.3 WIRE RANGE: SEE TABLE

3. SUITABLE CONTACT: MP10A23*-25 & MP10A23*-63.

4. RoHS COMPLIANT.

5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

P/N	WIRE RANGE	CONTACT PLATING(MATING AREA)
MS10A23S-25	1.5~2.5mm ²	SILVER PLATING OVER NICKEL.
MS10A23F-25	1.5~2.5mm ²	GOLD FLASH PLATING OVER NICKEL.
MS10A23S-63	4~6mm ²	SILVER PLATING OVER NICKEL.
MS10A23F-63	4~6mm ²	GOLD FLASH PLATING OVER NICKEL.

[illegible]

TITLE: EconMate RM, SOCKET CONTACT, MACHINE, 8# (Ø3.6mm)

DWG NO

MS10A23*-25/63

REV: **A4**

SH: 1

OF:	
-----	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MS10A23S-25](#)