




NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:

1.1. CONTACT BODY: COPPER ALLOY.

1.2. POSITIONING CLIP: STAINLESS STEEL.

2. SPECIFICATIONS:

2.1 CURRENT RATING : 7.5A(MAX).

2.2 TERMINATION TYPE: CRIMPING.

2.3 CRIMP WIRE RANGE: 22~20AWG.

3. ALL DIMENSION ARE FOR REFERENCE USE ONLY.

4. ROHS COMPLIANT.

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
B1	-	RELEASED DRAWING	JULY-1-2014	BEN	TOMMY

P/N	CONTACT PLATING(MATING AREA)
MS20W23F	GOLD FLASH PLATING OVER NICKEL.
MS20W23G10	10μ"GOLD PLATING OVER NICKEL.
MS20W23G15	15μ"GOLD PLATING OVER NICKEL.
MS20W23G30	30μ"GOLD PLATING OVER NICKEL.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference =		SIGNATURES DRAWN: BEN CHECKED: ENGINEER: APPROVAL: DATE: JULY-1-2014	
MATERIAL SPECIFICATIONS:		CUSTOMER:	
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
NEXT ASSY:		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 ECO-MATE, SOCKET CONTACT MACHINE, 22-20AWG, SIZE 20 SIZE: B C- DWG NO: MS20W23xx SCALE: NONE SHEET 1 OF 1	

TITLE: ECO-MATE SOCKET CONTACT MACHINE, 22-20AWG, SIZE 20
DWG NO: MS20W23xx
REV: B1
SH: 1
OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MS20W23F](#)