






XX: No. Of Pin—




3P



4P




5P



8P

Pin Assignments Front View

UNIT: mm



TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^{\circ}$

TITLE	
N SEN, MI2 A -SHLD, SCREW	
CABLE W/O SR, F, F, FI SCREW IN	

SCALE 1 : 1	SIZE A4	SHEET 1 OF 1
REV. B	WC-REV. A.3	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Mila	DATE 2015-09-23
DWG NO MSAS-XXBFFB-SL7001	CHECKED BY Cary	DATE 2015-09-23
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-09-23

 Note:

- * RoHS Compliant
- *  Important Dimension
- * Waterproof rate: IPX7, mated
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - Extension Nut: Metal
 - Nut: Metal
 - O-Ring: Rubber, Gray
- * Clamp Ring: Metal
- * O-Ring: Rubber, Gray
- * Clamp Cage: Thermoplastic, Black
- * Sealing Nut: Metal
- * Seal: Rubber, Gray, OD: $\varnothing 4.0\text{mm} \sim \varnothing 7.5\text{mm}$
- * One set unassembled in one pe bag

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MSAS-08BFFB-SL7001](#)

[MSAS-04BFFB-SL7001](#)

[MSAS-03BFFB-SL7001](#)

[MSAS-05BFFB-SL7001](#)