


TITLE: 22 PB LITE, 4 PIN, M/F, 14AWG, TC-ER/STOOW, PVC	DWG NO: C-P29008-Mxxx	REV: A1	SH: 1	OF: 1
--	-----------------------	---------	-------	-------



4) RoHS COMPLIANT
5) UL 2237 LISTED ASSEMBLY
UL FILE NUMBERS: E339703

Amphenol P/N	ROCKWELL P/N	MOLEX	TURCK
P29008-M*	280-PWRM24A-M*	114030A46M*	RSMRKM44-*M
P29008-M1	280-PWRM24A-M010	114030A46M010	RSMRKM44-010M
P29008-M2	280-PWRM24A-M020	114030A46M020	RSMRKM44-020M
P29008-M3	280-PWRM24A-M030	114030A46M030	RSMRKM44-030M
P29008-M5	280-PWRM24A-M050	114030A46M050	RSMRKM44-050M
P29008-M10	280-PWRM24A-M100	114030A46M100	RSMRKM44-100M

TOLERANCE	
0-2.99 M = +100.0/-25.0mm	0-9.99 FT = +4" / -1"
3-8.99 M = +150.0/-25.0mm	10.00-29.99 FT = +6" / -1"
9-14.99 M = +300.0/-25.0mm	30.00-49.99 FT = +12" / -1"
15-OVER M = +450.0/-25.0mm	50 FT-OVER = +18" / -1"

PART NUMBER		DESCRIPTION		ITEM
QUANTITY	MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED: 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ± 0.30 2 PL DEC ± 0.15 3 PL DEC ± 0.08 3) Note reference = 		SIGNATURES DATE DRAWN: KMM 12-MAY-14 CHECKED: MRF 12-MAY-14 ENGINEER: KMM APPROVAL: RFC 12-MAY-14 CUSTOMER:		Amphenol Sine Systems - www.amphenol-sine.com 44724 Mingo Drive Clinton Township, MI 48036
MATERIAL SPECIFICATIONS: PROCESS SPECIFICATIONS:		M22 POWERBOSS LITE, 4 PIN, M/F, 14 AWG, TC-ER/STOOW, PVC JACKET		
THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		SIZE TYPE C-	DWG NO: P29008-Mxxx	REVISION A1
NEXT ASSY:		SCALE: FULL	C-P29008	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[P29008-M15](#)