






REV.	ECON NO.	DATE	SIGN	DESCRIPTION



4	Black	4
3	Blue	3
2	White	2
1	Brown	1
Conn.1	Wire Color	Conn.2

Pin Out

UNIT:mm	
---------	---

TITLE			
M12P BCoded Conn			
T Cable Screw MF Conn MF Pin			
SCALE	Free	SHEET	1 OF 1
REV.	A	SIZE	A4
QC :inspection Item			

 $\pm 0.5 \text{ mm}$

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO PB-040400-MF0-TSAXX	Kenneth James	2007/12/07
CHECKED BY		DATE
Ricky Valerio		2007/12/07
CUSTOMER	APPROVED BY	DATE
ALTW	Cloud	2008/01/04


Note:

- * **②** Important Dimension.
- * Waterproof Rate: IP68
- * Housing: Black, Polyurethane
- * Screw Nut: Black, Nylon+GF
- * Male Pin: Copper Alloy, Gold Plated
- * Female Pin: Copper Alloy, Gold Plated
- * Wire Harness: UL1007 24AWG, 4Pcs
- * Cable: UL2464 22AWG*4C+Talc
- * Black, PVC Jacket UV Resistant OD=5.0mm
- * Cable Length Tolerance: 1M~10M±5%mm, 11M~99±500mm.

Cable Length(L):01~99Meters

99:99Meters

XX:01 ~99Meter
01:01Meter
02:02Meters



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PB-040400-MF0-TSA10](#) [PB-040400-MF0-TSA02](#) [PB-040400-MF0-TSA05](#) [PB-040400-MF0-TSA01](#)