



5	Blue (24AWG) 藍	5	Twist
4	White (24AWG) 白	4	
3	Black (22AWG) 黑	3	Twist
2	Red (22AWG) 紅	2	
1	Drain (22AWG) 地線	1	
Conn.1	Wire Color	Conn.2	
Pin Out			

- * @@ Important Dimension.
- * Waterproof Rate: IP68
- * Connector: Polyurethane (PU), Black
- * Female Pin: Copper Alloy, Gold Plated
- * Cable: Black, (24#*1P+A)+(22#*1P+A)+Drain+AL.Mylar+Braid
PVC UV Cable OD=6.0mm
- * Cable Length Tolerance: 1M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE			Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO		DRAWN BY		DATE		
TOLERANCE		M12P Conn NMEA 1 Adapt Screw FF Conn FF Pin				DWG NO		CHECKED BY		DATE		
±0.5 mm		SCALE		SHEET		PC-000505-0FF-CSAXX		Rita		2016/06/30		
		REV.	SIZE	QC : Inspection Item		CUSTOMER		APPROVED BY		DATE		
		B	A4			ALTW		Lisa		2016/06/30		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PC-000505-OFF-CSA01](#) [PC-000505-OFF-CSA02](#) [PC-000505-OFF-CSA05](#) [PC-000505-OFF-CSA10](#)