



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1510501-05	2015/01/19	Jinhai	Change Logo

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



000505-0MM-CSAX
X
ALT
XX:01~99Meters
01:01Meter
02:02Meter
:
:
99:99Meters
Cable Length(L):01~99Meters

Notes:

- * ~~Qc~~Important Dimension.
- * Waterproof Rate: IP68.
In 1 meter water within 24 hours.
- * Connector: Polyurethane (PU), Black
- * Male Pin:Copper Alloy,Gold Plated.
- * Cable: (24#*IP+A)+(22#*IP+A)+Drain+AL.Mylar
+Braid PVC UV Cable OD=6.0mm, Black
- * Cable Length Tolerance: $0.1M \pm 40mm$
 $0.2M \sim 0.5M: \pm 60mm$
 $0.6M \sim 1.0M: \pm 100mm$
 $1.1M \sim 3.0M: \pm 200mm$
 $3.1M \sim 9.9M: \pm 500mm$

A	UNIT:mm			TITLE	M12P Conn NMEA 1 Adapt Screw MM Conn MM Pin	Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO	Jinhai	DRAWN BY	DATE	2015-01-19
	TOLERANCE	± 0.5		SCALE	3:2	SIZE	A4	SHEET	1 OF 1	CHECKED BY	Tom
	REV.	B	WC-REV.	A.1	(QC)	Inspection item	PC-000505-0MM-CSAXX	CUSTOMER	ALTW	APPROVED BY	Jerry
		2		3	4	5	6	7	8	FMW10702-01-02A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PC-000505-0MM-CSA10](#) [PC-000505-0MM-CSA02](#) [PC-000505-0MM-CSA05](#) [PC-000505-0MM-CSA01](#)