




REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Green	5	5
Black	4	4
Blue	3	3
White	2	2
Brown	1	1
Wire Color	Conn.1	Conn.2



Pin Out

Note: Cable Length(L):01~99Meters

* @C Important Dimension.

* Waterproof Rate: IP67

* Housing: Black, Polyurethane

* Nut: Black, Nylon+GF

* Pin: Copper Alloy, Gold Plated


* O-Ring: Green, Viton

* Wire Harness: UL1007 24AWG,(5Pcs.)

* Cable: Black,UL2464 22AWG*5C+Talc

PVC Jacket UV Resistant OD=5.5mm

* Cable Length Tolerance:1M~10M±5%mm,11M~99±500mm.



UNIT:mm		TITLE	M12 Conn T Cable Screw	ITEM NO	DRAWN BY	DATE
TOLERANCE		SCALE	MF Conn C Pin	DWG NO	CLOYD Grezula	2007/12/03
±0.5 mm		REV. A	Free size A4	CUSTOMER	CHECKED BY	DATE
1			@C :inspection item	AL TW	Robert Dabu	2007/12/07
2					APPROVED BY	DATE
3					Cloud	2008/01/04
4						
5						
6						
7						
8						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PI-050500-KZ0-TSA02](#) [PI-050500-KZ0-TSA01](#) [PI-050500-KZ0-TSA05](#) [PI-050500-KZ0-TSA10](#)