




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2012/10/25	Ruru	PLD-02BMFA-QL7001 To PLD-02BMFA-QL7001
B	LEN1510150	2015/01/08	Vicky	Update Logo & Tolerance



Recommended Torque: 1.5Kgf-cm Min.



- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP67.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Housing: Nylon, UL 94V-0, Black.
 - * Seal: Silicone, UL 94V-0, Gray.
 - * Clamp Ring: Nylon, UL 94V-2, Black.
 - * Sealing Nut: Nylon, UL 94V-2, Black.
 - * Seal for Cable OD: $\varnothing 4.5\text{mm} \sim \varnothing 6.5\text{mm}$.
 - * Operating Voltage Max: AC 300 V Rms.
 - * Operating Current Max: 5A.
 - * One Set Unassembled In One Bag.

UNIT:mm				TITLE ASSY,PUSH LOCK,2PIN M CONN F PIN			Amphenol LTW		ITEM NO PLD-02BMFA-QL7001		DRAWN BY Vicky		DATE 2015-01-08						
TOLERANCE ±0.5 mm						SCALE 3:2			SIZE A4		SHEET 1 OF 1			DWG NO PLD-02BMFA-QL7001		CHECKED BY Sam		DATE 2015-01-08	
						REV. B			WC-REV. A.2		QC: Inspection item			CUSTOMER ALTW		APPROVED BY Rita		DATE 2015-01-08	
1		2		3		4		5		6		7		8		FWI 0702-01-02A1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PLD-02BMFA-QL7001](#)