




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2012/10/25	Ruru	PLI2-04BFMA-QL7001 To PLD-04BFMA-QL7001
B	LEN1510153	2015/01/08	Vicky	Update Logo & Tolerance



Recommended Torque: 1.5Kgf-cm Min.



Pin Assignments
Front View



- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP67.
 - * Housing: Nylon, UL 94V-0, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Nut: NYLON+25%GF, UL 94V-0, Black.
 - * Clamp Ring: Nylon+GF, UL 94V-2, Black.
 - * Sealing Nut: Nylon+GF, UL 94V-2, Black.
 - * Rubber Parts: Silicone, UL 94V-0, Gray.
 - * Seal for Cable OD: $\varnothing 4.5\text{mm} \sim \varnothing 6.5\text{mm}$.
 - * Operating Voltage Max: AC 300 V Rms.
 - * Operating Current Max: 5A.
 - * One Set Unassembled In One Bag.

UNIT:mm			TITLE ASSY,PUSH LOCK,4PIN F CONN M PIN				ITEM NO PLD-04BFMA-QL7001		DRAWN BY Vicky		DATE 2015-01-08				
TOLERANCE ±0.5 mm				SCALE 3:2	SIZE A4	SHEET 1	OF 1	DWG NO PLD-04BFMA-QL7001	CHECKED BY Sam	DATE 2015-01-08					
				REV. B	WC-REV. A.2	QC: Inspection item		CUSTOMER ALTW	APPROVED BY Rita	DATE 2015-01-08					
1		2		3		4		5		6		7		8 FMW10702-01-02A1	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PLD-04BFMA-QL7001](#)