





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2014/06/19	Tom	Change Rev. I To Rev. A



Conn.



Drain Wire	地線	Shield
Brown	棕	8
White/Brown	白/棕	7
Green	綠	6
White/Blue	白/藍	5
Blue	藍	4
White/Green	白/綠	3
Orange	橙	2
White/Orange	白/橙	1
Wire Color		Conn.
Pin Out		



Recommended Panel Cut-Out

RCP-5SAFFM-SLM7BXX
XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

Note:
* Important Dimension To Check.
* Waterproof Rate: IP67
* Connector : Nylon+GF, Black
* Cable : CAT5E FTP 24AWG*4P+My+Drain +AL/My (UV Resistant),OD=6.5mm, Black
* Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE	RJ45 Cable Screw Cat 5E F Conn F Pin	
TOLERANCE	±0.5	SCALE	1:1	SIZE A4
		REV.	A	WC-REV. A.3
			QC:Inspection item	

Amphenol LTW		ITEM NO	DRAWN BY	DATE
安費諾亮泰企業股份有限公司		DWG NO	Tom	2014-06-19
		CUSTOMER	Jerry	2014-06-19
			Victor	2014-06-19

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP-5SAFFM-SLM7B01](#)