



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1440191	2014/05/10	Tom	Updated The Note



RCP-5SAMMM-SLM7BXX

Pin Out		
Wire Color		Plug
Drain Wire	接地	Shield
Brown	棕	8
Brown/white	棕白	7
Green	綠	6
Blue/white	藍白	5
Blue	藍	4
Green/white	綠白	3
Orange	橙	2
Orange/white	橙白	1

XX: 01~99Meter
01: 01Meter
02: 02Meters
:
99: 99Meters
Cable Length(L):01~99Meters
X:
(B)CAT5E FTP

Note:
* Important Dimension
* Waterproof Rate:IP67.
* Plug:PC,UL94V-2,Gold Plated,Shielded
* Screw Nut:Nylon+GF,Black.
* Gasket:EPDM,Black.
* Cable: 24AWG*4P,Black,UV Resistant
(B)CAT5E FTP,OD Max.:Ø6.5.
* Cable Length Tolerance: 01M:±40mm
02~05M:±60mm
06~10M:±100mm
11~30M:±200mm
30~99M:±500mm

UNIT:mm		TITLE RJ45,C SIZE CABLE SCREW 5E M CONN M PIN	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	SCALE 1:1	SIZE A4	SHEET 1 OF 1
REV. B	WC-REV. B.3	Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Tom	DATE 2014-05-10
DWG NO RCP-5SAMMM-SLM7BXX	CHECKED BY Jerry	DATE 2014-05-10
CUSTOMER ALTW	APPROVED BY VICTOR	DATE 2014-05-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP-5SAMMM-SLM7B03](#)