




1	2	3	4	5	6	7	8
REV.	ECN NO.	DATE	SIGN	DESCRIPTION			



Pin Out

Wire Color		Plug	Twist 對絞
Drain Wire	接地	Shield	
Brown	棕	8	Twist 對絞
Brown/white	棕白	7	
Green	綠	6	Twist 對絞
Blue/white	藍白	5	
Blue	藍	4	Twist 對絞
Green/white	綠白	3	
Orange	橙	2	Twist 對絞
Orange/white	橙白	1	

RCP-5SAMMM-TLM7BXX

XX: 01~99Meter
01: 01Meter
02: 02Meters
:
:
99: 99Meters
Cable Length(L):01~99Meters

(B)CAT5E FTP

Note:

- * Important Dimension
- * Waterproof Rate: IP67.
- * Plug: PC, UL94V-2, Gold Plated, Shielded
- * Lock Nut: Nylon+GF, Black.
- * Gasket: EPDM, Black.
- * Cable: (B)CAT5E FTP, OD Max.: $\varnothing 6.5$, Black.
- * Cable Length Tolerance:
 - 01M: ± 40 mm
 - 02~05M: ± 60 mm
 - 06~10M: ± 100 mm
 - 11~30M: ± 200 mm
 - 30~99M: ± 500 mm

UNIT : mm			TITLE RJ45,C SIZE CABLE 3P_LOCK 5E M CONN M PIN			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Laurence_zang		DATE 2013-04-20	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±		SCALE 1 : 1	SIZE A4	SHEET 1 OF 1	DWG NO RCP-5SAMMM-TLM7BXX			CHECKED BY RAISON		DATE 2013-04-20			
		REV. A	WC-REV. A.8	QC: Inspection item	CUSTOMER ALTW			APPROVED BY VICTOR		DATE 2013-04-20			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP-5SAMMM-TLM7B05](#)