




REV.	ECN NO.	DATE	SIGN	DESCRIPTION



RCP-5UAMMM-TLM7AXX

XX: 01~99Meter
01: 01Meter
02: 02Meters
...

99: 99Meters

Cable Length(L):01~99Meters

X:
(A)CAT5E UTP

Note:

- * ⌀ Important Dimension
- * Waterproof Rate:IP67.
- * Plug:PC,UL94V-2,Gold Plated,
- * Lock Nut:Nylon+GF,Black.
- * Gasket:EPDM,Black.
- * Cable: (A)CAT5E UTP,OD Max.:Ø6.0,Black.
- * Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
30~99M: ±500mm

Pin Out		
Wire Color		Plug
Drain Wire	接地	
Brown	棕	8
Brown/white	棕白	7
Green	綠	6
Blue/white	藍白	5
Blue	藍	4
Green/white	綠白	3
Orange	橙	2
Orange/white	橙白	1

Twist
對絞

Twist
對絞

Twist
對絞

UNIT:mm		TITLE
TOLERANCE		RJ45,C SIZE CABLE
.X ±0.25		3P_LOCK 5E M CONN M PIN
.XX ±0.1		
.XXX ±0.05		
ANGLES ±1°		
SCALE	1:1	SIZE A4
REV.	A	WC-REV. A.11
		QC:Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Laurence_zang	2013-04-20
RCP-5UAMMM-TLM7AXX	CHECKED BY	DATE
CUSTOMER	RAISON	2013-04-20
ALTW	APPROVED BY	DATE
	VICTOR	2013-04-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP-5UAMMM-TLM7A10](#) [RCP-5UAMMM-TLM7A20](#)