




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1720074~075	2017-02-17	Feng_Li	Modify Note



Conn.1

Waterproof Rate: IP67




Conn.2

1 RCP-5SAMMM-SLM7000
COLOR: BLACK

2 Cable

3 Plug



RCP5SM-SPG06M-SL7B XX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
...

99 : 99Meters

Cable Length(L): 01~99Meters

Note:

- * $\varnothing$ Important Dimention To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Screw Nut: Nylon+GF, Black
- * RJ Plug: Shield, Phosphor Bronze, Gold Plated
- * Cable: CAT5E FTP 24#*4P+D+AL/MY, 6.5
- * Cable Length Tolerance:
 - 01M: ± 40 mm
 - 02M~05M: ± 60 mm
 - 06M~10M: ± 100 mm
 - 11M~30M: ± 200 mm
 - 31M~99M: ± 500 mm

Shield	Drain Wire	接地線	Shield
8	Brown	棕	8
7	White/Brown	白/棕	7
6	Green	綠	6
5	White/Blue	白/藍	5
4	Blue	藍	4
3	White/Green	白/綠	3
2	Orange	橘	2
1	White/Orange	白/橘	1
Conn.1	Wire Color		Conn.2

Pin Out

UNIT:mm		TITLE
TOLERANCE		RJ DOUBLE-ENDED, WITH PLUG
.X ± 0.25		SCALE 4:5
.XX ± 0.1		SIZE A4
.XXX ± 0.05		SHEET 1 OF 1
ANGLES $\pm 1^\circ$		REV. B
		WC-REV. A.1
		$\varnothing$ Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Feng_Li	2017-02-17
RCP5SM-SPG06M-SL7BXX	CHECKED BY	DATE
CUSTOMER	Jinhai	2017-02-17
ALTW	APPROVED BY	DATE
	Jerry	2017-02-17

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP5SM-SPG06M-SL7B20](#)