




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190683	2019-05-02	Allen	Update Note.




Conn.1

Waterproof Rate: IP67



Conn.2



RCP5SM-SPG06M-TL7B XX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters

Cable Length(L):01~99Meters

Note:

- * $\varnothing$ Important Dimention To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Lock Nut: Nylon+GF, Black
- * RJ Plug: Shield, Phosphor Bronze, Gold Plated
- * Cable: CAT5E FTP 24#*4P+D+AL/MY, 6.5
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

Shield	Drain Wire	Shield
8	Brown 棕	8
7	White/Brown 白/棕	7
6	Green 綠	6
5	White/Blue 白/藍	5
4	Blue 藍	4
3	White/Green 白/綠	3
2	Orange 橘	2
1	White/Orange 白/橘	1
Conn.1	Wire Color	Conn.2

Pin Out

UNIT:mm		TITLE
TOLERANCE		RJ DOUBLE-ENDED, WITH PLUG
.X ±0.25		SCALE 4:5
.XX ±0.1		SIZE A4
.XXX ±0.05		SHEET 1 OF 1
ANGLES ±1°		REV. B
		WC-REV. A.3
		$\varnothing$ Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Allen	2019-05-02
DWG NO	CHECKED BY	DATE
RCP5SM-SPG06M-TL7BXX	Jane	2019-05-02
CUSTOMER	APPROVED BY	DATE
ALTW	Neo	2019-05-02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP5SM-SPG06M-TL7B03](#)