




		REVISIONS		
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	06/02/27	L.CHAN
B		PER ECN E07135	JUN 5/07	L.CHAN
C		UPDATE PER ACTUAL PART.	OCT22/15	L.CHAN



FRONT VIEW



SIDE VIEW



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

MATERIALS:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL94V-0
COLOR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: MATING AREA: SELECTIVELY PLATED GOLD—PER
PART NUMBER OPTIONS
50 MICROINCH [1.27 MICRONS] MIN. NICKEL OVERALL
100 MICROINCH [2.54 MICRONS] MIN. MATTE TIN
OR GOLD FLASH OVER TAIL

AMPHENOL PART NUMBER: RJE07-188-0X10

GOLD PLATING
1 = 06 MICROINCH
2 = 15 MICROINCH
3 = 30 MICROINCH
4 = 50 MICROINCH



DRAWN PAULW	DATE 06/02/27	Amphenol Canada Corp.		
DESIGNED				
CHECKED CHIGOW	06/02/27	TITLE RJE07 SURFACE MOUNT MODULAR JACK 8 POSITION, 8 CONTACTS, WITHOUT SHIELD, WITHOUT FLANGE AND WITHOUT KEY – RoHS COMPLIANT		
I. E. APPRD. JEFF.S	JUN 5/07			
Q. A. APPRD. KENT.Y	JUN 5/07	DWG DRAWING NO. P-RJE07-188-0X10 REV. C		
DWG. APPRD.				
ENG. REL. NO. E07135		SCALE WT. _____ SURF. _____ SHEET 1 OF 1		
REF.				
DIMENSIONS ARE IN inches (mm)	CODE ID. NO. 03554			

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RJE07-188-3120](#) [RJE07-188-0110](#) [RJE07-188-0210](#) [RJE07-188-0310](#) [RJE07-188-0410](#) [RJE07-188-2120](#) [RJE07-188-2220](#) [RJE07-188-2420](#) [RJE07-188-3220](#) [RJE07-188-3320](#) [RJE07-188-3420](#) [RJE07-188-2320](#)